


## DiffRACTIVA-aA



on a scale of 5:1

HD-optic

## Technical Information

<b>Type</b>	Multifocal Posterior Chamber IOL (Single-Piece, Foldable)
<b>Material</b>	Hydrophilic Acrylic with UV-Absorber
<b>Water Content</b>	26% at 35°C
<b>Optic</b>	DiffRACTIVE Aspheric Anterior Surface (Aberration Free)* Spheric Posterior Surface with 360° Lens Epithelial Cell Barrier
<b>Haptic Shape</b>	C-Loop
<b>Optic Shape</b>	Biconvex
<b>Diopter Range</b>	10.0 to 30.0 D
<b>Diopter Steps</b>	0.5 D
<b>Near Addition</b>	+ 3.5 D (on IOL plane)
<b>A-Constant (est.)**</b>	118.4

## HumanOptics AG

Spardorferstraße 150  
91054 Erlangen

Phone: +49 (0) 9131 / 50665-0  
Fax: +49 (0) 9131 / 50665-90

www.humanoptics.com  
mail@humanoptics.com

\* The word „aberration“ as used in this document is interpreted as „spherical aberration“

\*\* For current status and more details please refer to [www.humanoptics.com](http://www.humanoptics.com)