


Secura-sSA



on a scale of 5:1

Technical Information

Type	Posterior Chamber IOL (Three-Piece, Foldable) for Sulcus Fixation	
Optic Material	Silicone Elastomer with UV-Absorber	
Haptic Material	High Molecular PMMA	
Haptic Shape	Modified C-Loop	
Optic Shape	Spheric Anterior Surface, Aspheric Posterior Surface (Aberration Correcting)*	
	Biconvex	
Dioptr Range	7.0 to 31.0 D	32.0 to 40.0 D
Dioptr Steps	0.5 D	1.0 D
	More details on dioptr categories see page 2	
A-Constant (est.)**	118.0	

HumanOptics AG

Spardorferstraße 150
91054 Erlangen

Phone: +49 (0) 9131 / 50665-0
Fax: +49 (0) 9131 / 50665-90

www.humanoptics.com
mail@humanoptics.com

03/2011

* The word „aberration“ as used in this document is interpreted as „spherical aberration“

** For current status and more details please refer to www.humanoptics.com



Dioptr Category – Secura-sSA

Standard	7.0 to 31.0 D	in 0.5 D steps
Special	32.0 to 40.0 D	in 1.0 D steps

The dioptr category does not indicate any conclusion related to availability. The delivery time of single powers might vary and is subject to change.